

## **MLAC33 BTA to DIN Adapter Cable**

### *Accessories*

MLAC33 BTA to DIN Adapter Cable (200 mm long). Provides connection for Vernier transducers to PowerLab Pod inputs. Works with most powered Vernier transducers.

Does not operate with Vernier temperature probes. Does not operate with PowerLab Bridge Amps.



#### **Caution**

Read “Statement of Intended Use” on our website or in “Getting Started with PowerLab” before use.

#### **Ordering Information:**

MLAC33 BTA to DIN Adapter Cable

For use with:

PowerLabs with Pod Ports